

# Dimensions

## Enclosure Styles

### Tier 1

Drive plus one or both of the following:

- Fuses
- Disconnect

### Tier 2

Drive with bypass or up to two of the following:

- Contactor motor selection
- dV/dt filter
- Input AC line reactor
- Dual motor control

### Tier 3

Drive with bypass and up to two of the following:

- Contactor motor selection
- dV/dt filter (NEMA 1 only)
- Input AC line reactor (NEMA 1 only)
- Dual motor control



		NEMA 1		NEMA12	NEMA 1 and NEMA 12							
		A2	A3	A5	B1	B2	C1	C2	D1	D2	E1	
Drive Only	Height	14.8	14.8	16.5	18.9	25.6	26.9	30.2	47.5 / 55.4*	62.4 / 68.3*	78.7	
	Width	5.2	5.2	9.5	9.5	9.5	12.1	14.6	16.5	16.5	22.8	
	Depth	8.7**	8.7**	10.2	10.2	10.2	12.2	13	14.7	14.7	19.4	
Tier 1	Height	19.1	19.1	16.5	18.9	25.6	26.9	30.2	47.5	62.4	78.7	
	Width	5.2	5.2	9.5	9.5	9.5	12.1	14.6	16.5	16.5	22.8	
	Depth	8.7	8.7	10.2	10.2	10.2	12.2	13	14.7	14.7	19.4	
	w/ disconnect	9.6	9.6	12	12	12	14.1	14.9	16.4	16.4	21.2	
Tier 2	Height	31.8	31.8	16.5	18.9	25.6	26.9	30.2	47.5	62.4	Consult Factory	
	Width	5.2	5.2	19.1	19.1	19.1	24.2	29.3	33.1	33.1	Consult Factory	
	Depth	9.6	9.6	12	12	12	14.1	14.9	16.4	16.4	Consult Factory	
Tier 3	NEMA 1											
	Height	31.8	31.8	16.5	18.9	25.6	26.9	30.2	47.5	62.4	Consult Factory	
	Width	5.2	5.2	28.7	28.7	28.7	36.4	44	49.6	49.6	Consult Factory	
	Depth	9.6	9.6	12	12	12	14.1	14.9	16.4	16.4	Consult Factory	

\* Height for wall mount / height when mounted on pedestal  
 \*\* Depth increased by .55" when an option A or B card is added